

COMPACTA

1530POO040P30

EAN 4031582429275



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

HOUSING

Material fork	Steel sheet, light
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	One ball race
Offset	16 mm
Swivel radius	36 mm
Swivel interference	72 mm

FITTING

Fitting type	Bolt hole
Bolt hole diameter	10 mm

CORE ATTRIBUTES

Product name	Compacta
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	55 mm
Overall weight	0.11 kg

WHEEL

Body material	Polypropylene
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Riveted
Threadguards	Without threadguard
Diameter	40 mm
Hardness of tread (A)	95 Shore A