

DURATECH

MOP 250X50-Ø40 HL60

EAN 4031582320077
Order number 00801034



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide, super heavy |
| Tread material | Identical with wheel body |
| Bearing | Precision ball bearing |
| Wheel color | Natural white |
| Threadguards | Without threadguard |
| Diameter | 9.84 in |
| Tread width | 1.97 in |
| Axle hole diameter | 1.57 in |
| Hub length | 2.36 in |
| Body width | 1.97 in |
| Hardness of tread (D) | 75 Shore D |
| Bearing type | 6308 |

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ○ ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|------------------------------|
| Product name | Duratech |
| Type | Wheel |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 2.5 mph | 9259.4 lb |
| Load capacity at 3.7 mph | 7716.17 lb |
| Load capacity Static | 18518.81 lb |
| Temperature range (Minimum) | -40 °F |
| Temperature range (Maximum) | 176 °F |
| Overall weight | 8.58 lb |

DURATECH

MOP 250X50-Ø40 HL60

EAN 4031582320077
Order number 00801034



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

