

LUMINA

AA23YOI050B10-11X20/10 9011/9011

EAN 4031582341232
Order number 00071380



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●○○
Corrosion resistance	●●●○○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel castor with intermittend brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Electric conductive	✓
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	55 mm
Overall width	55 mm
Overall weight	0.11 kg

WHEEL

Body material	Polypropylene, electric conductive
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Graphite black (RAL9011)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	8 mm
Axle hole diameter	0 mm
Hub length	0 mm
Body width	8 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Polypropylene
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Colour	Graphite black (RAL9011)
Offset	20 mm
Swivel radius	52 mm
Swivel interference	104 mm
Dome diameter	0 mm

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm
Stem length	20 mm

PRODUCT INFORMATION

LUMINA

AA23YOI050B10-11X20/10 9011/9011

EAN 4031582341232
Order number 00071380



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

