

MAXTECH

PNP200X50-Ø8 HL60 GRIS

EAN 4031582452778



Image may differ from the original product

WHEEL

Body material	Polypropylene
Tread hardness	soft
Tread material	Polyurethane, foamed
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	200 mm
Tread width	50 mm
Axle hole diameter	8 mm
Hub length	60 mm
Hardness of tread (A)	70 Shore A

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Maxtech
Type	Wheel
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall weight	0.065 kg

MAXTECH

PNP200X50-Ø8 HL60 GRIS

EAN 4031582452778



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

