

# LINEA

5940XSP125R05-22 RAL9002

EAN 4031582352009



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Linea                     |
| Type                        | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 1.8 mph    | 286.6 lb                  |
| Electric conductive         | ✓                         |
| Load capacity Static        | 573.2 lb                  |
| Temperature range (Minimum) | 14 °F                     |
| Temperature range (Maximum) | 104 °F                    |
| Overall height              | 5.71 in                   |
| Overall width               | 3.23 in                   |
| Overall weight              | 2.12 lb                   |

## WHEEL

|                       |   |
|-----------------------|---|
| Body material         | Polyamide, electric conductive              |
| Tread material        | Polyurethane, injected, electric-conductive |
| Bearing               | Precision ball bearing                      |
| Threadguards          | With threadguard                            |
| Diameter              | 4.92 in                                     |
| Tread width           | 0.79 in                                     |
| Hardness of tread (A) | 92 Shore A                                  |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Material            | Polyamide              |
| Fork shape          | Twin wheel housing     |
| Swivel bearing      | Precision ball bearing |
| Color               | Gray white (RAL9002)   |
| Offset              | 1.57 in                |
| Swivel radius       | 4.29 in                |
| Swivel interference | 8.58 in                |
| Dome diameter       | 2.05 in                |

## FITTING

|               |                   |
|---------------|-------------------|
| Fitting type  | Solid stem, round |
| Bolt diameter | 0.87 in           |
| Bolt length   | 1.57 in           |



Deutscher Designer Club



Interzum Award



IF Design Award

# LINEA

5940XSP125R05-22 RAL9002

EAN 4031582352009



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

