

GALEA STAINLESS

5087PIO125P30-12

EAN 4031582370959



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Galea stainless
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	176.37 lb
Stainless	✓
Load capacity Static	352.74 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	6.38 in
Overall weight	1.19 lb

WHEEL

Body material	Polypropylene
Tread material	Solid rubber, non-marking
Bearing	Plain bearing
Threadguards	Without threadguard
Diameter	4.92 in
Tread width	1.18 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Polyamide
Fork shape	Closed
Swivel bearing	Two ball races, reinforced or stainless
Offset	1.57 in
Swivel interference	8.07 in

FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.47 in

GALEA STAINLESS

5087PIO125P30-12

EAN 4031582370959



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

