

# LUMINA

A523YOI050B10-11X20 DOM45

EAN 4031582341423



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## HOUSING

Material fork	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Swivel radius	51 mm
Swivel interference	102 mm
Dome diameter	45 mm

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm

## CORE ATTRIBUTES

Product name	Lumina
Housing type	Swivel castor with intermittent brake
Standard	EN12528 - Furniture Castors
Electric conductive	✓
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	61 mm
Overall width	55 mm
Overall weight	0.093 kg

## WHEEL

Body material	Polypropylene, electric conductive
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	50 mm
Tread width	8 mm
Hardness of tread (D)	65 Shore D

PRODUCT INFORMATION

# LUMINA

A523YOI050B10-11X20 DOM45

EAN 4031582341423



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

