

LINEA LIGHT

5920XSI075L51-10 7001/7015/1016

EAN 4031582399066



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Linea light
Type	Swivel caster
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	176.37 lb
Electric conductive	Yes
Stainless	no
Load capacity Static	352.74 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	2.97 in
Overall width	2.17 in
Overall weight	0.33 lb

HOUSING

Housing Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Housing Color	Silver gray (RAL7001)
Offset	0.91 in
Swivel radius	2.56 in
Swivel interference	5.12 in
Dome diameter	1.18 in

WHEEL

Body material	Polyamide, electric conductive
Tread material	Polyurethane, injected, electric-conductive
Bearing	Plain bearing with spacer tube
Tread color	Slate gray (RAL7015)
Wheel color	Slate gray (RAL7015)
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.59 in
Axle hole diameter	0 in
Hub length	0 in
Body width	0.59 in
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	0.39 in

Deutscher
Designer
ClubInterzum
Awardproduct
design
awardIF Design
Award

LINEA LIGHT

5920XSI075L51-10 7001/7015/1016


EAN 4031582399066

Order number 00770551

Product Drawings



BETTER MOBILITY. BETTER LIFE.



Deutscher
Designer
Club



Interzum
Award



product
design
award

IF Design
Award