

LUMINA

A520UJI050L51-8

EAN 4031582431872



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll Performance | ● ● ● ● ○ |
| Movement Noise | ● ● ● ● ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-----------------------------|
| Product Name | Lumina |
| Type | Swivel castor |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 40 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 80 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall Height | 56 mm |
| Overall width | 54 mm |
| Overall weight | 0.08 kg |

HOUSING

| | |
|---------------------|---------------------------------------|
| Housing Material | Polypropylene |
| Fork shape | Twin wheel housing, closed, with dome |
| Swivel Bearing | Stem, swiveling |
| Swivel radius | 48 mm |
| Swivel interference | 96 mm |

WHEEL

| | |
|-----------------------|--------------------------------|
| Body material | Polyamide |
| Tread Material Mix | Thermoplastic rubber |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 50 mm |
| Tread width | 10 mm |
| Hardness of tread (A) | 87 Shore A |

FITTING

| | |
|--------------------|--------------------|
| Fitting type | Blind hole for B10 |
| Bolt hole diameter | 8 mm |

LUMINA

A520UJI050L51-8

EAN 4031582431872



BETTER MOBILITY. BETTER LIFE.

Product Drawings

