

# LINEA LIGHT

A920PJI075L51-10 RAL9002

EAN 4031582377637



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ● ●

## CORE ATTRIBUTES

Product name	Linea light
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	60 kg
Load capacity Static	120 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	75.5 mm
Overall width	55 mm
Overall weight	0.134 kg

## WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	75 mm
Tread width	15 mm
Hardness of tread (A)	92 Shore A

## HOUSING

Material fork	Polypropylene
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	23 mm
Swivel radius	65 mm
Swivel interference	130 mm
Dome diameter	30 mm

## FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	10 mm



# LINEA LIGHT



A920PJI075L51-10 RAL9002

EAN 4031582377637



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS



Deutscher  
Designer  
Club



Interzum  
Award



IF  
Design  
Award