

LUMINA

5520UAI075S70-12X25-11 RAL9006



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Lumina
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	88 mm
Overall width	65 mm
Overall weight	0.28 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	75 mm
Tread width	10 mm
Body width	10 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing, closed, with dome
Swivel bearing	Stem, swiveling
Colour	White aluminium (RAL9006)
Offset	30 mm
Swivel radius	73 mm
Swivel interference	146 mm
Dome diameter	45 mm

FITTING

Fitting type	Threaded stem with hexagon neck, top
Bolt hole diameter	11 mm
Stem diameter	12 mm

LUMINA

5520UAI075S70-12X25-11 RAL9006



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

