

LINEA

594CUAP125P52 RAL9002

EAN 4031582378375



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-------------|
| Roll Performance | ● ● ● ● ● ● |
| Movement Noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|----------------------------------|
| Product Name | Linea |
| Type | Swivel castor with combined lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 3 km/h | 130 kg |
| Electric Conductive | No |
| Stainless | No |
| Load capacity Static | 260 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 60 °C |
| Overall Height | 148.5 mm |
| Overall width | 82 mm |
| Overall weight | 1.12 kg |
| Certification | Tested and monitored by TÜV Süd |

HOUSING

| | |
|---------------------|------------------------|
| Housing Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel Bearing | Precision ball bearing |
| Housing Color | Grey white (RAL9002) |
| Offset | 40 mm |
| Swivel radius | 129 mm |
| Swivel interference | 258 mm |
| Dome diameter | 52 mm |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Polyamide |
| Tread Material Mix | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Threadguards | With threadguard |
| Diameter | 125 mm |
| Tread width | 20 mm |
| Hardness of tread (A) | 92 Shore A |

FITTING

| | |
|-----------------------------|---|
| Fitting type | Rectangular plate, US-bolt hole spacing |
| Plate length | 95 mm |
| Plate width | 70 mm |
| Plate hole length (Minimum) | 72 mm |
| Plate hole length (Maximum) | 76 mm |
| Plate hole width (Minimum) | 44.5 mm |
| Plate hole width (Maximum) | 52 mm |
| Plate hole diameter | 11 mm |



Deutscher Designer Club



Interzum Award



IF Design Award



Product Drawings

