

# AGILA

2470POO050P30 Black TZA

EAN 4031582489453



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Agila                     |
| Type                        | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 50 kg                     |
| Electric Conductive         | No                        |
| Stainless                   | No                        |
| Load capacity Static        | 100 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall Height              | 69 mm                     |
| Overall weight              | 0.16 kg                   |



BETTER MOBILITY. BETTER LIFE.

## HOUSING

|                  |                     |
|------------------|---------------------|
| Housing Material | Steel sheet, medium |
| Fork shape       | Broad               |
| Swivel Bearing   | Two ball races      |
| Housing Color    | Blue passivated     |
| Offset           | 24 mm               |
| Swivel radius    | 49 mm               |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Body material         | Polypropylene             |
| Tread Material Mix    | Identical with wheel body |
| Bearing               | Plain bearing             |
| Threadguards          | Without threadguard       |
| Diameter              | 50 mm                     |
| Tread width           | 20 mm                     |
| Hardness of tread (D) | 65 Shore D                |

## FITTING

|                    |                                                            |
|--------------------|------------------------------------------------------------|
| Fitting type       | Bolt hole                                                  |
| Bolt hole diameter | 11 mm                                                      |
| Hint               | Castors can be mounted with standard screws of any length. |

# AGILA

2470POO050P30 Black TZA

EAN 4031582489453



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

---

