

KAPPA

9680MOP080P63

EAN 4031582429022



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	●●●●○
Movement noise	●●●○
Attrition	●●●●○
Corrosion resistance	●●●○

CORE ATTRIBUTES

Product name	Kappa
Housing type	Swivel castor
Load capacity at 3 km/h	1200 kg
Load capacity at 4 km/h	1200 kg
Load capacity at 6 km/h	1000 kg
Load capacity Static	2000 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	135 mm
Overall width	110 mm
Overall weight	3.193 kg

WHEEL

Body material	Polyamide, super heavy
Tread material	Identical with wheel body
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	80 mm
Tread width	60 mm

HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	41 mm
Swivel radius	81 mm
Swivel interference	162 mm

FITTING

Fitting type	Rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

TECHNICAL DRAWINGS

