

# NOVATECH

ETY 070x20-Ø20 HL12

EAN 4031582331233



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Novatech                      |
| Type                        | Wheel                         |
| Standard                    | EN12532 - Transport Equipment |
| Load capacity at 2.5 mph    | 264.55 lb                     |
| Load capacity at 3.7 mph    | 220.46 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 529.11 lb                     |
| Temperature range (Minimum) | 14 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall weight              | 0.34 lb                       |

## WHEEL

|                       |                                 |
|-----------------------|---------------------------------|
| Body material         | Steel, iron                     |
| Tread material        | Polyurethane, casted            |
| Bearing               | Precision ball bearing (RS/2RS) |
| Wheel color           | Honey yellow (RAL1005)          |
| Threadguards          | With threadguard                |
| Diameter              | 2.76 in                         |
| Tread width           | 0.79 in                         |
| Axle hole diameter    | 0.79 in                         |
| Hub length            | 0.47 in                         |
| Body width            | 0.79 in                         |
| Hardness of tread (A) | 92 Shore A                      |
| Hardness of tread (D) | 42 Shore D                      |

