

AGILA

2477PJO075R07-19/21,5

EAN 4031582326253
Order number 00062085



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ●
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Type	Swivel castor with total lock
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	132.28 lb
Load capacity Static	264.55 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	4.06 in
Overall width	1.69 in
Overall weight	0.83 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing
Wheel color	Silver gray (RAL7001)
Threadguards	Without threadguard
Diameter	2.95 in
Tread width	0.98 in
Body width	0.98 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Color	Blue passivated
Offset	0.94 in
Swivel radius	3.15 in
Swivel interference	6.3 in
Dome diameter	1.69 in

FITTING

Fitting type	Synthetic expander, round
Stem length	0.87 in
Expander fitting (Minimum)	0.75 in
Expander fitting (Maximum)	0.87 in
Hint	Please indicate required tube innerdiameter when ordering.

AGILA

2477PJO075R07-19/21,5

EAN 4031582326253
Order number 00062085



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

