

# AGILA

2477PIP100P30-11

EAN 4031582362039



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Agila                         |
| Type                        | Swivel caster with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 1.8 mph    | 176.37 lb                     |
| Electric conductive         | no                            |
| Stainless                   | no                            |
| Load capacity Static        | 352.74 lb                     |
| Temperature range (Minimum) | -4 °F                         |
| Temperature range (Maximum) | 140 °F                        |
| Overall height              | 5.31 in                       |
| Overall weight              | 1.68 lb                       |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Housing Material    | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Housing Color       | Blue passivated     |
| Offset              | 1.71 in             |
| Swivel radius       | 5.16 in             |
| Swivel interference | 10.31 in            |

## WHEEL

|                       |                           |
|-----------------------|---------------------------|
| Tread hardness        | soft                      |
| Body material         | Polypropylene             |
| Tread material        | Solid rubber, non-marking |
| Bearing               | Precision ball bearing    |
| Threadguards          | With threadguard          |
| Diameter              | 3.94 in                   |
| Tread width           | 1.26 in                   |
| Hardness of tread (A) | 75 Shore A                |

## FITTING

|                    |  |
|--------------------|--|
| Fitting type       | Bolt hole  |
| Bolt hole diameter | 0.43 in  |
| Hint               | Castors can be mounted with standard screws of any length. |

# AGILA

2477PIP100P30-11

EAN 4031582362039



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

