

# NOVATECH

ITB160X50-Ø20

EAN 4031582443851



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## WHEEL

Body material	Aluminum
Tread material	Polyurethane, casted
Bearing	Bore with keyway
Threadguards	Without threadguard
Diameter	6.3 in
Tread width	1.97 in
Axle hole diameter	0.79 in
Hub length	2.13 in
Hardness of tread (A)	92 Shore A

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Novatech
Housing type	Wheel
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	2116.44 lb
Load capacity at 3.7 mph	1763.7 lb
Load capacity Static	4232.87 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall weight	10.2 lb

## TECHNICAL DRAWINGS

