

AGILA

2470PJP100R47-27-30

EAN 4031582325324



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Load capacity Static	440.92 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	5.43 in

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	3.94 in
Tread width	1.26 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	1.5 in
Swivel radius	3.46 in
Swivel interference	6.93 in

FITTING

Fitting type	Synthetic expander, square
Expander fitting (Minimum)	1.06 in
Expander fitting (Maximum)	1.18 in
Hint	Please indicate required tube innerdiameter when ordering.

AGILA

2470PJP100R47-27-30

EAN 4031582325324



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

