

# LUMINA

5525UAI075L51-11 ~9006/9011/~9006/9011

EAN 4031582310672



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                                |
|-----------------------------|--------------------------------|
| Product Name                | Lumina                         |
| Type                        | Swivel castor with wheel brake |
| Standard                    | EN12528 - Furniture Castors    |
| Load capacity at 3 km/h     | 100 kg                         |
| Electric Conductive         | No                             |
| Stainless                   | No                             |
| Load capacity Static        | 200 kg                         |
| Temperature range (Minimum) | -20 °C                         |
| Temperature range (Maximum) | 60 °C                          |
| Overall Height              | 88 mm                          |
| Overall width               | 65 mm                          |
| Overall weight              | 0.3 kg                         |

## HOUSING

|                     |                                       |
|---------------------|---------------------------------------|
| Housing Material    | Polyamide                             |
| Fork shape          | Twin wheel housing, closed, with dome |
| Swivel Bearing      | Stem, swiveling                       |
| Housing Color       | White aluminium (RAL9006)             |
| Offset              | 30 mm                                 |
| Swivel radius       | 106 mm                                |
| Swivel interference | 212 mm                                |
| Dome diameter       | 45 mm                                 |

## WHEEL

|                       |                                |
|-----------------------|--------------------------------|
| Body material         | Polyamide                      |
| Tread Material Mix    | Polyurethane, injected         |
| Bearing               | Plain bearing with spacer tube |
| Axle                  | Riveted                        |
| Tread Color           | Graphite black (RAL9011)       |
| Wheel Color           | White aluminium (RAL9006)      |
| Threadguards          | Without threadguard            |
| Diameter              | 75 mm                          |
| Tread width           | 10 mm                          |
| Axle Hole Diameter    | 0 mm                           |
| Hub Length            | 0 mm                           |
| Body width            | 10 mm                          |
| Hardness of tread (A) | 92 Shore A                     |

## FITTING

|                    |                    |
|--------------------|--------------------|
| Fitting type       | Blind hole for B10 |
| Bolt hole diameter | 11 mm              |

# LUMINA

5525UAI075L51-11 ~9006/9011/~9006/9011

EAN 4031582310672

Order number 00074380

**Product Drawings**



BETTER MOBILITY. BETTER LIFE.

