



Image may differ from the original product

**PERFORMANCE**

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

**CORE ATTRIBUTES**

|                             |                                       |
|-----------------------------|---------------------------------------|
| Product name                | Linea                                 |
| Type                        | Swivel caster                         |
| Standard                    | similar EN12531- Hospital Bed Castors |
| Load capacity at 1.8 mph    | 330.69 lb                             |
| Load capacity at 2.5 mph    | 330.69 lb                             |
| Electric conductive         | Yes                                   |
| Stainless                   | no                                    |
| Load capacity Static        | 661.39 lb                             |
| Temperature range (Minimum) | -4 °F                                 |
| Temperature range (Maximum) | 176 °F                                |
| Overall height              | 5.12 in                               |
| Overall width               | 2.8 in                                |
| Overall weight              | 2.04 lb                               |

**HOUSING**

|                     |                        |
|---------------------|------------------------|
| Housing Material    | Polyamide              |
| Fork shape          | Twin wheel housing     |
| Swivel bearing      | Precision ball bearing |
| Offset              | 1.57 in                |
| Swivel radius       | 4.04 in                |
| Swivel interference | 8.07 in                |

**WHEEL**

|                |                                             |
|----------------|---------------------------------------------|
| Body material  | Polyamide                                   |
| Tread material | Polyurethane, injected, electric-conductive |
| Bearing        | Precision ball bearing, stainless           |
| Threadguards   | With threadguard                            |
| Diameter       | 4.92 in                                     |
| Tread width    | 0.59 in                                     |

**FITTING**

|               |                   |
|---------------|-------------------|
| Fitting type  | Solid stem, round |
| Bolt diameter | 1.26 in           |
| Bolt length   | 1.77 in           |

# LINEA


5940USC125R05-32

EAN 4031582360097



BETTER MOBILITY. BETTER LIFE.

## Product Drawings



Deutscher  
Designer  
Club



Interzum  
Award



product  
design  
award

IF Design  
Award