

AGILA CARE

2474PJP100R36-32S30 D 4XM6

EAN 4031582301632
Order number 00027696



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Agila care
Housing type	Swivel castor with central, total or directional lock
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	138 mm
Overall width	60 mm
Overall weight	0.832 kg

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Precision ball bearing
Wheel color	Silver grey (RAL7001)
Threadguards	With threadguard
Diameter	100 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Blue passivated
Offset	38 mm
Swivel radius	88 mm
Swivel interference	176 mm
Dome diameter	60 mm

FITTING

Fitting type	Stem with cam hole for profile bars, short version
Bolt diameter	32 mm
Bolt length	51 mm
Bolt thread position	7 mm
Bolt mounting holes quantity	4

PRODUCT INFORMATION

AGILA CARE

2474PJP100R36-32S30 D 4XM6

EAN 4031582301632
Order number 00027696



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

