

LUMINA

6A20YGI050L51-10 ZAMAK/9011/9011

EAN 4031582335804
Order number 00079236



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Lumina
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Electric conductive	✓
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	56 mm
Overall width	55 mm
Overall weight	0.115 kg

WHEEL

Body material	Polypropylene, electric conductive
Tread material	Thermoplastic rubber, electric-conductive
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Graphite black (RAL9011)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	10 mm
Body width	10 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material	Zinc-die-casting / Aluminium
Fork shape	Twin wheel housing, closed
Swivel bearing	Stem, swiveling
Offset	20 mm
Swivel radius	54 mm
Swivel interference	108 mm

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	10 mm

PRODUCT INFORMATION

LUMINA

6A20YGI050L51-10 ZAMAK/9011/9011

EAN 4031582335804
Order number 00079236



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

