

DELTA TWIN

9940ETP065P41-100X100

EAN 4031582501162
Order number 00800241



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Delta twin
Type	Swivel castor
Standard	EN12532 - Transport Equipment
Load capacity at 2.5 mph	881.85 lb
Load capacity Static	1763.7 lb
Temperature range (Minimum)	-22 °F
Temperature range (Maximum)	140 °F
Overall height	4.39 in
Overall width	3.62 in
Overall weight	4.26 lb

WHEEL

Body material	Steel, iron
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Honey yellow (RAL1005)
Threadguards	With threadguard
Diameter	2.56 in
Tread width	1.18 in
Body width	1.18 in
Hardness of tread (A)	92 Shore A
Hardness of tread (D)	42 Shore D

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Color	Transparent coating
Offset	0.98 in
Swivel radius	2.44 in
Swivel interference	4.88 in
Dome diameter	2.87 in

FITTING

Fitting type	Square plate
Plate length	3.94 in
Plate width	3.94 in
Plate hole length (Minimum)	2.48 in
Plate hole length (Maximum)	3.07 in
Plate hole width (Minimum)	2.48 in
Plate hole width (Maximum)	3.07 in
Plate hole diameter	0.41 in

DELTA TWIN

9940ETP065P41-100X100

EAN 4031582501162
Order number 00800241



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

