

# ZETA REVERSE

468SITP125P63 SOFT CV

EAN 4031582398373  
Order number 00860896



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Zeta reverse
Type	Swivel castor with spring loaded directional lock
Standard	EN12532 - Transport Equipment
Load capacity at 4 km/h	400 kg
Load capacity at 6 km/h	320 kg
Load capacity Static	800 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	60 °C
Overall height	164 mm
Overall width	96 mm
Overall weight	2.97 kg

## WHEEL

Body material	Aluminium
Tread hardness	soft
Tread profile	convex
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Wheel color	Traffic grey A (RAL7042)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	50 mm
Body width	50 mm
Hardness of tread (A)	80 Shore A

## HOUSING

Material fork	Steel sheet, very heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Colour	Blue passivated
Offset	55 mm
Swivel radius	117.5 mm
Swivel interference	235 mm
Dome diameter	96 mm

## FITTING

Fitting type	Medium rectangular plate
Plate length	137 mm
Plate width	105 mm
Plate hole length (Minimum)	75 mm
Plate hole length (Maximum)	80 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	11 mm

# ZETA REVERSE

468SITP125P63 SOFT CV

EAN 4031582398373  
Order number 00860896



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

