

# INTEGRAL TWIN

2940UAP100R05-28

EAN 4031582338584



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Integral twin
Type	Swivel castor
Standard	similar EN12531- Hospital Bed Castors
Load capacity at 3 km/h	125 kg
Load capacity at 4 km/h	125 kg
Load capacity Static	250 kg
Temperature range (Minimum)	-30 °C
Temperature range (Maximum)	80 °C
Overall height	129 mm
Overall width	60 mm
Overall weight	1.093 kg
Certification	Tested and monitored by TÜV Süd

## WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	15 mm
Hardness of tread (D)	42 Shore D

## HOUSING

Material fork	Steel sheet, medium
Fork shape	Twin wheel housing
Swivel bearing	Precision ball bearing
Offset	31 mm
Swivel radius	81 mm
Swivel interference	162 mm

## FITTING

Fitting type	Solid stem, round
Bolt diameter	28 mm
Bolt length	45 mm



German Design Award



Red Dot Design Award

# INTEGRAL TWIN

2940UAP100R05-28


EAN 4031582338584



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---



German  
Design  
Award



Red Dot  
Design  
Award