

# AGILA CARE

2474PJO150R26-28S45 4XM8

EAN 4031582301601



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ○ ○ |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ○ ○ |

## CORE ATTRIBUTES

|                             |   |
|-----------------------------|---|
| Product name                | Agila care  |
| Housing type                | Swivel castor with central, total or directional lock |
| Standard                    | EN12530 - Devices Castors                             |
| Load capacity at 3 km/h     | 100 kg  |
| Load capacity Static        | 200 kg  |
| Temperature range (Minimum) | -20 °C  |
| Temperature range (Maximum) | 60 °C   |
| Overall height              | 188 mm  |
| Overall weight              | 1.02 kg   |

## WHEEL

|                       |                      |
|-----------------------|----------------------|
| Body material         | Polypropylene        |
| Tread material        | Thermoplastic rubber |
| Bearing               | Plain bearing        |
| Threadguards          | Without threadguard  |
| Diameter              | 150 mm               |
| Tread width           | 32 mm                |
| Hardness of tread (A) | 87 Shore A           |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Material fork       | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel bearing      | Two ball races      |
| Offset              | 45 mm               |
| Swivel radius       | 120 mm              |
| Swivel interference | 240 mm              |

## FITTING

|               |                                     |
|---------------|-------------------------------------|
| Fitting type  | Stem with cam hole for profile bars |
| Bolt diameter | 28 mm                               |
| Bolt length   | 96 mm                               |

# AGILA CARE

2474PJO150R26-28S45 4XM8

EAN 4031582301601



BETTER MOBILITY. BETTER LIFE.

## TECHNICAL DRAWINGS

---

