

AGILA

2470DYK050B10-11x31

EAN 4031582341089



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Agila
Type	Swivel caster
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	88.18 lb
Electric conductive	Yes
Stainless	no
Load capacity Static	176.37 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	185 °F
Overall height	2.83 in
Overall width	1.69 in
Overall weight	0.52 lb

HOUSING

Housing Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Housing Color	Blue passivated
Offset	0.94 in
Swivel radius	1.93 in
Swivel interference	3.86 in
Dome diameter	1.61 in

WHEEL

Body material	Sheet Steel
Tread material	Solid rubber, black, electric-conductive
Bearing	Cone ball bearing
Threadguards	With threadguard
Diameter	1.97 in
Tread width	0.75 in
Body width	0.75 in
Hardness of tread (A)	80 Shore A

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	0.43 in
Stem length	1.22 in

AGILA

2470DYK050B10-11x31

EAN 4031582341089

Order number 00005184

Product Drawings



BETTER MOBILITY. BETTER LIFE.

