

LINEA LIGHT

A920PJI075L51-10 RAL7001

EAN 4031582377644



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ●
Movement Noise	● ● ● ● ●
Attrition	● ● ● ● ●
Corrosion Resistance	● ● ● ● ●

CORE ATTRIBUTES

Product Name	Linea light
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	60 kg
Electric Conductive	No
Stainless	No
Load capacity Static	120 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	75.5 mm
Overall width	55 mm
Overall weight	0.15 kg

HOUSING

Housing Material	Polypropylene
Fork shape	Twin wheel housing
Swivel Bearing	Stem, swiveling
Housing Color	Silver grey (RAL7001)
Offset	23 mm
Swivel radius	65 mm
Swivel interference	130 mm
Dome diameter	30 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	75 mm
Tread width	15 mm
Hardness of tread (A)	92 Shore A

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	10 mm



Deutscher
Designer
Club



Interzum
Award



product
design
award

IF Design
Award

LINEA LIGHT

A920PJ1075L51-10 RAL7001

EAN 4031582377644



BETTER MOBILITY. BETTER LIFE.

Product Drawings

