

ANIKA

5925UAI075L51-10 DOM18

EAN 4031582455465



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Anika
Housing type	Swivel castor with wheel brake
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	50 kg
Load capacity Static	100 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall height	77.2 mm
Overall width	41.5 mm
Overall weight	0.14 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Plain bearing with spacer tube
Axle	Riveted
Threadguards	Without threadguard
Diameter	75 mm
Tread width	11 mm

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	24 mm
Swivel radius	87.7 mm
Swivel interference	175.4 mm
Dome diameter	18 mm

FITTING

Fitting type	Blind hole for B10 fitting
Bolt hole diameter	10 mm



ANIKA

5925UAI075L51-10 DOM18

EAN 4031582455465



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

