

KAPPA

9681FVP300P64

EAN 4031582315516



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Kappa
Housing type	Swivel castor with directional lock
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	960 kg
Load capacity at 6 km/h	800 kg
Load capacity Static	1920 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	85 °C
Overall height	355 mm
Overall weight	23.027 kg

WHEEL

Body material	Cast iron
Tread material	Solid rubber, black
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	300 mm
Tread width	85 mm
Hardness of tread (A)	70 Shore A

HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Two ball races, reinforced or stainless
Offset	70 mm
Swivel interference	262 mm

FITTING

Fitting type	Rectangular plate
Plate length	175 mm
Plate width	140 mm
Plate hole length (Maximum)	140 mm
Plate hole width (Maximum)	105 mm
Plate hole diameter	15 mm

KAPPA

9681FVP300P64

EAN 4031582315516



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

