

LINEA

5947XSC100P30-13 RAL9002

EAN 4031582352542



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Linea |
| Type | Swivel castor with total lock |
| Standard | EN12530 - Devices Castors |
| Load capacity at 1.8 mph | 264.55 lb |
| Electric conductive | ✓ |
| Stainless | ✓ |
| Load capacity Static | 529.11 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 4.65 in |
| Overall width | 3.23 in |
| Overall weight | 1.6 lb |

WHEEL

| | |
|-----------------------|---|
| Body material | Polyamide, electric conductive |
| Tread material | Polyurethane, injected, electric-conductive |
| Bearing | Precision ball bearing, stainless |
| Threadguards | With threadguard |
| Diameter | 3.94 in |
| Tread width | 0.79 in |
| Hardness of tread (A) | 92 Shore A |

HOUSING

| | |
|---------------------|------------------------|
| Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Precision ball bearing |
| Color | Gray white (RAL9002) |
| Offset | 1.26 in |
| Swivel radius | 4.25 in |
| Swivel interference | 8.5 in |
| Dome diameter | 2.05 in |

FITTING

| | |
|--------------------|-----------|
| Fitting type | Bolt hole |
| Bolt hole diameter | 0.51 in |



LINEA


5947XSC100P30-13 RAL9002

EAN 4031582352542



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS



Deutscher
Designer
Club



Interzum
Award



IF
Design
Award