

LINEA SMART

5920UAP100S70-M12X25 SMART RAL9002

EAN 4031582433333



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Movement noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Linea smart
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	90 kg
Load capacity Static	180 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	119 mm
Overall width	72 mm
Overall weight	0.5 kg

WHEEL

Body material	Polyamide
Tread material	Polyurethane, injected
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	100 mm
Tread width	20 mm
Hardness of tread (A)	92 Shore A

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Offset	32 mm
Swivel radius	88 mm
Swivel interference	176 mm
Thread diameter	12 mm

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	25 mm



Deutscher Designer Club



Interzum Award



IF Design Award