

KAPPA LOAD

9650TOO125P63

EAN 4031582348743
Order number 00838705



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ●
Movement noise	● ○ ○ ○ ○
Attrition	● ● ● ● ●
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Kappa load
Housing type	Swivel castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 4 km/h	840 kg
Load capacity at 6 km/h	700 kg
Load capacity Static	1680 kg
Temperature range (Minimum)	-40 °C
Temperature range (Maximum)	80 °C
Overall height	170 mm
Overall weight	3 kg

WHEEL

Body material	Polyamide, heavy
Tread material	Identical with wheel body
Bearing	Plain bearing
Axle	Screwed with nut
Threadguards	Without threadguard
Diameter	125 mm
Tread width	50 mm
Hardness of tread (D)	75 Shore D

HOUSING

Material fork	Iron forged, heavy
Fork shape	Broad, reinforced
Swivel bearing	Deep-groove ball thrust roller bearing
Offset	48 mm
Swivel radius	110.5 mm
Swivel interference	221 mm

FITTING

Fitting type	Rectangular plate
Plate length	135 mm
Plate width	110 mm
Plate hole length (Maximum)	105 mm
Plate hole width (Minimum)	75 mm
Plate hole width (Maximum)	80 mm
Plate hole diameter	11 mm

KAPPA LOAD

9650TOO125P63

EAN 4031582348743
Order number 00838705



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

