

STYLEA

5923XOI065B10-11X20/10D23 9011/9011

EAN 4031582343588
Order number 00079444



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	●●●○○
Movement noise	●●●○○
Attrition	●●●●●
Corrosion resistance	●●●●○

CORE ATTRIBUTES

Product name	Stylea
Type	Swivel castor with intermittend brake
Standard	EN12529 - Swivel Chairs Castors
Load capacity at 3 km/h	50 kg
Electric conductive	✓
Load capacity Static	100 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	68 mm
Overall width	43 mm
Overall weight	0.126 kg

WHEEL

Body material	Polyamide, electric conductive
Tread material	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread color	Graphite black (RAL9011)
Wheel color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	65 mm
Tread width	8 mm
Axle hole diameter	0 mm
Hub length	0 mm
Body width	8 mm
Hardness of tread (D)	65 Shore D

HOUSING

Material fork	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Colour	Graphite black (RAL9011)
Offset	25 mm
Swivel radius	53 mm
Swivel interference	106 mm
Dome diameter	23 mm

FITTING

Fitting type	Stem with grip ring, with collar
Stem diameter	11 mm
Stem length	20 mm

PRODUCT INFORMATION

STYLEA

5923XOI065B10-11X20/10D23 9011/9011

EAN 4031582343588
Order number 00079444



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

