

STYLEA

5925UAP075P40 60X60 RAL9002 TFR

EAN 4031582394504



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|--------------------------------|
| Product name | Stylea |
| Type | Swivel castor with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 1.8 mph | 176.37 lb |
| Load capacity Static | 352.74 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 104 °F |
| Overall height | 2.95 in |
| Overall width | 2.13 in |

WHEEL

| | |
|----------------|------------------------|
| Body material | Polyamide |
| Tread material | Polyurethane, injected |
| Bearing | Precision ball bearing |
| Axle | Riveted |
| Threadguards | With threadguard |
| Diameter | 2.95 in |
| Tread width | 0.59 in |

HOUSING

| | |
|---------------------|----------------------|
| Material | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Color | Gray white (RAL9002) |
| Offset | 0.91 in |
| Swivel radius | 3.19 in |
| Swivel interference | 6.38 in |
| Dome diameter | 1.18 in |

FITTING

| | |
|-----------------------------|--------------|
| Fitting type | Square plate |
| Plate length | 2.36 in |
| Plate width | 2.36 in |
| Plate hole length (Maximum) | 1.89 in |
| Plate hole width (Maximum) | 1.89 in |

PRODUCT INFORMATION

STYLEA

5925UAP075P40 60X60 RAL9002 TFR

EAN 4031582394504



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

