

KAPPA LOAD

9652TOP200P63 CL67

EAN 4031582314946
Order number 00828520



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ○ ○ ○ |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|---|
| Product name | Kappa load |
| Type | Swivel castor with total lock, head end of castor |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 2.5 mph | 2645.54 lb |
| Load capacity at 3.7 mph | 2204.62 lb |
| Load capacity Static | 4409.24 lb |
| Temperature range (Minimum) | -22 °F |
| Temperature range (Maximum) | 176 °F |
| Overall height | 9.65 in |
| Overall width | 4.57 in |
| Overall weight | 11.7 lb |

WHEEL

| | |
|-----------------------|---------------------------|
| Body material | Polyamide, heavy |
| Tread material | Identical with wheel body |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Wheel color | Natural white |
| Threadguards | Without threadguard |
| Diameter | 7.87 in |
| Tread width | 1.97 in |
| Body width | 1.97 in |
| Hardness of tread (D) | 75 Shore D |

HOUSING

| | |
|---------------------|--|
| Material | Cast iron, or iron forged, heavy |
| Fork shape | Broad, reinforced |
| Swivel bearing | Deep-groove ball thrust roller bearing |
| Color | Blue passivated |
| Offset | 2.32 in |
| Swivel radius | 6.3 in |
| Swivel interference | 12.6 in |
| | ✓ |
| Dome diameter | 4.37 in |

FITTING

| | |
|-----------------------------|-------------------|
| Fitting type | Rectangular plate |
| Plate length | 5.31 in |
| Plate width | 4.33 in |
| Plate hole length (Minimum) | 2.95 in |
| Plate hole length (Maximum) | 3.15 in |
| Plate hole width (Minimum) | 2.95 in |
| Plate hole width (Maximum) | 4.13 in |
| Plate hole diameter | 0.43 in |

KAPPA LOAD

9652TOP200P63 CL67

EAN 4031582314946
Order number 00828520



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

