

KAPPA

9688IEP300P63 CL67

EAN 4031582348651
Order number 00838187



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ● ● |
| Movement noise | ● ● ● ● ● |
| Attrition | ● ● ● ● ● |
| Corrosion resistance | ● ● ● ● ● |

CORE ATTRIBUTES

| | |
|-----------------------------|-------------------------------|
| Product name | Kappa |
| Type | Fixed castor |
| Standard | EN12532 - Transport Equipment |
| Load capacity at 4 km/h | 600 kg |
| Load capacity at 6 km/h | 480 kg |
| Load capacity Static | 1200 kg |
| Temperature range (Minimum) | -20 °C |
| Temperature range (Maximum) | 85 °C |
| Overall height | 355 mm |
| Overall width | 98 mm |
| Overall weight | 6.343 kg |

WHEEL

| | |
|-----------------------|---------------------------------|
| Body material | Aluminium |
| Tread hardness | soft |
| Tread material | Elastic tire, black, vulcanized |
| Bearing | Precision ball bearing |
| Axle | Screwed with nut |
| Wheel color | Jet black (similar RAL9005) |
| Threadguards | Without threadguard |
| Diameter | 300 mm |
| Tread width | 55 mm |
| Body width | 55 mm |
| Hardness of tread (A) | 68 Shore A |

HOUSING

| | |
|--------------------|--------------------|
| Material fork | Iron forged, heavy |
| Fork shape | Broad, reinforced |
| Colour | Blue passivated |
| Lubrication nipple | ✓ |
| Dome diameter | 96 mm |

FITTING

| | |
|-----------------------------|--------------------------|
| Fitting type | Medium rectangular plate |
| Plate length | 135 mm |
| Plate width | 110 mm |
| Plate hole length (Minimum) | 75 mm |
| Plate hole length (Maximum) | 80 mm |
| Plate hole width (Minimum) | 75 mm |
| Plate hole width (Maximum) | 105 mm |
| Plate hole diameter | 11 mm |

KAPPA

9688IEP300P63 CL67

EAN 4031582348651
Order number 00838187



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

