

NOVATECH

ITP160X50-Ø47X12 CONVEX TFR

EAN 4031582429626



BETTER MOBILITY. BETTER LIFE.

PERFORMANCE

| | |
|----------------------|-----------|
| Roll performance | ● ● ● ○ ○ |
| Movement noise | ● ● ● ○ ○ |
| Attrition | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ○ ○ |

CORE ATTRIBUTES

| | |
|-----------------------------|------------------------------|
| Product name | Novatech |
| Housing type | Wheel |
| Standard | EN12533 - Heavy Duty Castors |
| Load capacity at 2.5 mph | 1322.77 lb |
| Load capacity at 3.7 mph | 1102.31 lb |
| Load capacity Static | 2645.54 lb |
| Temperature range (Minimum) | 14 °F |
| Temperature range (Maximum) | 140 °F |
| Overall weight | 1.74 lb |

WHEEL

| | |
|-----------------------|------------------------|
| Body material | Aluminum |
| Tread material | Polyurethane, casted |
| Bearing | Precision ball bearing |
| Threadguards | Without threadguard |
| Diameter | 6.3 in |
| Tread width | 1.97 in |
| Hub length | 2.13 in |
| Hardness of tread (A) | 92 Shore A |
| Ball bearing diameter | 1.85 in |
| Ball bearing width | 0.47 in |

NOVATECH

ITP160X50-Ø47X12 CONVEX TFR

EAN 4031582429626



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

