

# AGILA

2470PJO075P30-11

EAN 4031582010398



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ○ |
| Movement Noise       | ● ● ● ● ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Agila                     |
| Type                        | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 75 kg                     |
| Electric Conductive         | No                        |
| Stainless                   | No                        |
| Load capacity Static        | 150 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall Height              | 100 mm                    |
| Overall width               | 43 mm                     |
| Overall weight              | 0.21 kg                   |

## HOUSING

|                     |                     |
|---------------------|---------------------|
| Housing Material    | Steel sheet, medium |
| Fork shape          | Broad               |
| Swivel Bearing      | Two ball races      |
| Housing Color       | Blue passivated     |
| Offset              | 24 mm               |
| Swivel radius       | 61.5 mm             |
| Swivel interference | 123 mm              |
| Dome diameter       | 43 mm               |

## WHEEL

|                       |                       |
|-----------------------|-----------------------|
| Body material         | Polypropylene         |
| Tread Material Mix    | Thermoplastic rubber  |
| Bearing               | Plain bearing         |
| Wheel Color           | Silver grey (RAL7001) |
| Threadguards          | Without threadguard   |
| Diameter              | 75 mm                 |
| Tread width           | 25 mm                 |
| Body width            | 25 mm                 |
| Hardness of tread (A) | 87 Shore A            |

## FITTING

|                    |  |
|--------------------|--|
| Fitting type       | Bolt hole  |
| Bolt hole diameter | 11 mm  |
| Hint               | Castors can be mounted with standard screws of any length. |

# AGILA

2470PJO075P30-11

EAN 4031582010398

Order number 00003349  
Product Drawings



BETTER MOBILITY. BETTER LIFE.

