PRODUCT INFORMATION

MONO

5020PJH080S70-10X15 TFR

EAN 4031582385755



Image may differ from the original product

PERFORMANCE

Roll Performance	●●●○○
Movement Noise	●●●○○
Attrition	●●●○○
Corrosion Resistance	●●●●○

CORE ATTRIBUTES

Product Name	Mono
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	70 kg
Electric Conductive	No
Stainless	No
Load capacity Static	140 kg
Temperature range (Minimum)	-10 °C
Temperature range (Maximum)	40 °C
Overall Height	110 mm
Overall weight	0.18 kg

HOUSING

Housing Material	Polyamide
Fork shape	Closed
Swivel Bearing	Stem, swiveling
Offset	34 mm
Swivel radius	74 mm
Swivel interference	148 mm
Thread diameter	0 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Thermoplastic rubber
Bearing	Plain bearing
Threadguards	With threadguard
Diameter	80 mm
Tread width	24 mm
Hardness of tread (A)	87 Shore A

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem diameter	10 mm
Stem length	15 mm

© Copyright 2026 TENTE International GmbH


MONO

5020PJH080S70-10X15 TFR

EAN 4031582385755

BETTER MOBILITY. BETTER LIFE.

Product Drawings



© Copyright 2026 TENTE International GmbH