

AGILA STAINLESS

7470YGO125P50

EAN 4031582377354



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ● ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ●

CORE ATTRIBUTES

Product name	Agila stainless
Housing type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 3 km/h	100 kg
Electric conductive	✓
Load capacity Static	200 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall height	160 mm
Overall width	60 mm
Overall weight	0.637 kg

WHEEL

Body material	Polypropylene, electric conductive
Tread material	Thermoplastic rubber, electric-conductive
Bearing	Plain bearing
Wheel color	Silver grey (similar RAL7001)
Threadguards	Without threadguard
Diameter	125 mm
Tread width	32 mm
Body width	32 mm
Hardness of tread (A)	87 Shore A

HOUSING

Material fork	Stainless steel, medium
Fork shape	Broad
Swivel bearing	Two ball races
Colour	Stainless steel
Offset	41 mm
Swivel radius	103.5 mm
Swivel interference	207 mm
Stainless	✓

FITTING

Fitting type	Rectangular plate
Plate length	77 mm
Plate width	67 mm
Plate hole length (Minimum)	46.5 mm
Plate hole length (Maximum)	51.5 mm
Plate hole width (Minimum)	56 mm
Plate hole width (Maximum)	61.5 mm
Plate hole diameter	8.5 mm

AGILA STAINLESS

7470YGO125P50

EAN 4031582377354



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

