

OMIKRON TWIN

9958FTP250P66 TFR

EAN 4031582394320



BETTER MOBILITY. BETTER LIFE.




Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ● ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ● ○
Corrosion resistance	● ● ● ○ ○

CORE ATTRIBUTES

Product name	Omikron twin
Housing type	Fixed castor
Standard	EN12533 - Heavy Duty Castors
Load capacity at 2.5 mph	6349.31 lb
Load capacity at 3.7 mph	5291.09 lb
Load capacity Static	12698.61 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	12.8 in

WHEEL

Body material	Casting
Tread material	Polyurethane, casted
Bearing	Precision ball bearing
Axle	Screwed with nut
Threadguards	With threadguard
Diameter	9.84 in
Tread width	1.97 in
Hardness of tread (A)	92 Shore A

HOUSING

Material	Cast iron, or iron forged, heavy
Fork shape	Twin wheel housing

FITTING

Fitting type	Rectangular plate
Plate length	9.84 in
Plate width	7.87 in
Plate hole length (Maximum)	8.27 in
Plate hole width (Maximum)	6.3 in
Plate hole diameter	0.67 in