



Image may differ from the original product

**PERFORMANCE**

|                      |           |
|----------------------|-----------|
| Roll Performance     | ● ● ● ● ● |
| Movement Noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion Resistance | ● ● ● ● ○ |

**CORE ATTRIBUTES**

|                             |                           |
|-----------------------------|---------------------------|
| Product Name                | Linea                     |
| Type                        | Swivel castor             |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 3 km/h     | 130 kg                    |
| Electric Conductive         | Yes                       |
| Stainless                   | Yes                       |
| Load capacity Static        | 260 kg                    |
| Temperature range (Minimum) | -20 °C                    |
| Temperature range (Maximum) | 60 °C                     |
| Overall Height              | 143 mm                    |
| Overall width               | 82 mm                     |

**HOUSING**

|                     |                        |
|---------------------|------------------------|
| Housing Material    | Polyamide              |
| Fork shape          | Twin wheel housing     |
| Swivel Bearing      | Precision ball bearing |
| Housing Color       | Grey white (RAL9002)   |
| Offset              | 40 mm                  |
| Swivel radius       | 109 mm                 |
| Swivel interference | 218 mm                 |
| Dome diameter       | 52 mm                  |

**WHEEL**

|                       |                                             |
|-----------------------|---------------------------------------------|
| Body material         | Polyamide, electric conductive              |
| Tread Material Mix    | Polyurethane, injected, electric-conductive |
| Bearing               | Precision ball bearing, stainless           |
| Tread Color           | Slate grey (RAL7015)                        |
| Wheel Color           | Slate grey (RAL7015)                        |
| Threadguards          | With threadguard                            |
| Diameter              | 125 mm                                      |
| Tread width           | 20 mm                                       |
| Body width            | 20 mm                                       |
| Hardness of tread (A) | 92 Shore A                                  |

**FITTING**

|                    |           |
|--------------------|-----------|
| Fitting type       | Bolt hole |
| Bolt hole diameter | 13 mm     |

# LINEA

5940XSC125P30-13 RAL9002


EAN 4031582352504



BETTER MOBILITY. BETTER LIFE.

## Product Drawings

---



Deutscher  
Designer  
Club



Interzum  
Award



product  
design  
award

IF Design  
Award