

LUMINA

A520POI050L51-8 chrome/9011

EAN 4031582317312



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll Performance	● ● ● ● ○
Movement Noise	● ● ● ● ○
Attrition	● ● ● ● ○
Corrosion Resistance	● ● ● ● ○

CORE ATTRIBUTES

Product Name	Lumina
Type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 3 km/h	40 kg
Electric Conductive	No
Stainless	No
Load capacity Static	80 kg
Temperature range (Minimum)	-20 °C
Temperature range (Maximum)	60 °C
Overall Height	56 mm
Overall width	54 mm
Overall weight	0.05 kg

HOUSING

Housing Material	Polypropylene
Fork shape	Twin wheel housing, closed, with dome
Swivel Bearing	Stem, swiveling
Housing Color	Chrome
Offset	20 mm
Swivel radius	52 mm
Swivel interference	104 mm

WHEEL

Body material	Polypropylene
Tread Material Mix	Identical with wheel body
Bearing	Plain bearing with spacer tube
Axle	Riveted
Tread Color	Graphite black (RAL9011)
Wheel Color	Graphite black (RAL9011)
Threadguards	Without threadguard
Diameter	50 mm
Tread width	7 mm
Body width	7 mm
Hardness of tread (D)	65 Shore D

FITTING

Fitting type	Blind hole for B10
Bolt hole diameter	8 mm

PRODUCT INFORMATION

LUMINA

A520POI050L51-8 chrome/9011

EAN 4031582317312

Order number 00073005

Product Drawings



BETTER MOBILITY. BETTER LIFE.

