

# AGILA

2470PIP125P30-13

EAN 4031582334890



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ○ ○

## CORE ATTRIBUTES

Product name	Agila
Type	Swivel castor
Standard	EN12530 - Devices Castors
Load capacity at 1.8 mph	220.46 lb
Electric conductive	✓
Load capacity Static	440.92 lb
Temperature range (Minimum)	-4 °F
Temperature range (Maximum)	140 °F
Overall height	6.3 in
Overall weight	1.78 lb

## WHEEL

	soft
Tread material	Solid rubber, non-marking
Bearing	Precision ball bearing
Threadguards	With threadguard
Diameter	4.92 in
Tread width	1.26 in
Hardness of tread (A)	75 Shore A

## HOUSING

Material	Steel sheet, medium
Fork shape	Broad
Swivel bearing	Two ball races
Offset	1.61 in
Swivel radius	4.07 in
Swivel interference	8.15 in

## FITTING

Fitting type	Bolt hole
Bolt hole diameter	0.51 in
Hint	Castors can be mounted with standard screws of any length.

PRODUCT INFORMATION

# AGILA

2470PIP125P30-13

EAN 4031582334890



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---

