

LINEA LIGHT

5920PJI065S70-10X15 SCAN

EAN 4031582420555



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance	● ● ● ○ ○
Movement noise	● ● ● ○ ○
Attrition	● ● ● ○ ○
Corrosion resistance	● ● ● ● ○

CORE ATTRIBUTES

Product name	Linea light
Housing type	Swivel castor
Standard	EN12528 - Furniture Castors
Load capacity at 1.8 mph	55.12 lb
Load capacity Static	110.23 lb
Temperature range (Minimum)	14 °F
Temperature range (Maximum)	104 °F
Overall height	2.68 in
Overall width	1.81 in
Overall weight	0.26 lb

WHEEL

Body material	Polypropylene
Tread material	Thermoplastic rubber
Bearing	Plain bearing with spacer tube
Threadguards	Without threadguard
Diameter	2.56 in
Tread width	0.55 in
Hardness of tread (A)	87 Shore A

HOUSING

Material	Polyamide
Fork shape	Twin wheel housing
Swivel bearing	Stem, swiveling
Swivel radius	2.2 in
Swivel interference	4.41 in
Dome diameter	0.91 in
Thread diameter	0 in

FITTING

Fitting type	Threaded stem with hexagon neck, top
Stem length	0.59 in



LINEA LIGHT

5920PJI065S70-10X15 SCAN

EAN 4031582420555



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

