

STYLEA

5925UOI065L51-10 KICK PEDAL

EAN 4031582404067



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

Roll performance ●●●○○

Movement noise ●●●○○

Attrition ●●●○○

Corrosion resistance ●●●●○

CORE ATTRIBUTES

| | |
|-----------------------------|--------------------------------|
| Product name | Stylea |
| Type | Swivel castor with wheel brake |
| Standard | EN12528 - Furniture Castors |
| Load capacity at 3 km/h | 50 kg |
| Load capacity Static | 100 kg |
| Temperature range (Minimum) | -10 °C |
| Temperature range (Maximum) | 40 °C |
| Overall height | 68 mm |
| Overall width | 46 mm |
| Overall weight | 0.098 kg |

WHEEL

| | |
|----------------|--------------------------------|
| Body material | Polyamide |
| Tread material | Identical with wheel body |
| Bearing | Plain bearing with spacer tube |
| Axle | Riveted |
| Threadguards | Without threadguard |
| Diameter | 65 mm |
| Tread width | 13.9 mm |

HOUSING

| | |
|---------------------|--------------------|
| Material fork | Polyamide |
| Fork shape | Twin wheel housing |
| Swivel bearing | Stem, swiveling |
| Swivel radius | 67 mm |
| Swivel interference | 134 mm |
| Dome diameter | 23 mm |

FITTING

| | |
|--------------------|--------------------|
| Fitting type | Blind hole for B10 |
| Bolt hole diameter | 10 mm |

STYLEA

5925UOI065L51-10 KICK PEDAL

EAN 4031582404067



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

