

PRODUCT INFORMATION

MAXTECH

PNP300x42-Ø12 HL45

EAN 4031582411089



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

PERFORMANCE

|                      |             |
|----------------------|-------------|
| Roll Performance     | ● ● ● ● ○ ○ |
| Movement noise       | ● ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ ○ |
| Corrosion resistance | ● ● ● ● ○ ○ |

CORE ATTRIBUTES

|                             |                           |
|-----------------------------|---------------------------|
| Product name                | Maxtech                   |
| Type                        | Wheel                     |
| Standard                    | EN12530 - Devices Castors |
| Load capacity at 1.8 mph    | 154.32 lb                 |
| Electric conductive         | no                        |
| Stainless                   | no                        |
| Load capacity Static        | 308.65 lb                 |
| Temperature range (Minimum) | -4 °F                     |
| Temperature range (Maximum) | 140 °F                    |

WHEEL

|                       |                        |
|-----------------------|------------------------|
| Tread hardness        | soft                   |
| Body material         | Polypropylene          |
| Tread material        | Polyurethane, foamed   |
| Bearing               | Precision ball bearing |
| Threadguards          | With threadguard       |
| Diameter              | 11.81 in               |
| Tread width           | 1.65 in                |
| Axle hole diameter    | 0.47 in                |
| Hub length            | 1.77 in                |
| Hardness of tread (A) | 70 Shore A             |

