

# LINEA

5947UAC125P50 RAL9002

EAN 4031582353099



BETTER MOBILITY. BETTER LIFE.



Image may differ from the original product

## PERFORMANCE

|                      |           |
|----------------------|-----------|
| Roll performance     | ● ● ● ● ● |
| Movement noise       | ● ● ● ○ ○ |
| Attrition            | ● ● ● ● ○ |
| Corrosion resistance | ● ● ● ● ○ |

## CORE ATTRIBUTES

|                             |                               |
|-----------------------------|-------------------------------|
| Product name                | Linea                         |
| Housing type                | Swivel castor with total lock |
| Standard                    | EN12530 - Devices Castors     |
| Load capacity at 3 km/h     | 130 kg                        |
| Load capacity Static        | 260 kg                        |
| Temperature range (Minimum) | -10 °C                        |
| Temperature range (Maximum) | 40 °C                         |
| Overall height              | 148 mm                        |
| Overall width               | 82 mm                         |

## WHEEL

|                       |                                   |
|-----------------------|-----------------------------------|
| Body material         | Polyamide                         |
| Tread material        | Polyurethane, injected            |
| Bearing               | Precision ball bearing, stainless |
| Threadguards          | With threadguard                  |
| Diameter              | 125 mm                            |
| Tread width           | 20 mm                             |
| Hardness of tread (A) | 92 Shore A                        |

## HOUSING

|                     |                        |
|---------------------|------------------------|
| Material fork       | Polyamide              |
| Fork shape          | Twin wheel housing     |
| Swivel bearing      | Precision ball bearing |
| Offset              | 40 mm                  |
| Swivel radius       | 129 mm                 |
| Swivel interference | 258 mm                 |
| Dome diameter       | 52 mm                  |
| Stainless           | ✓                      |

## FITTING

|                             |                   |
|-----------------------------|-------------------|
| Fitting type                | Rectangular plate |
| Plate length                | 77 mm             |
| Plate width                 | 67 mm             |
| Plate hole length (Minimum) | 56 mm             |
| Plate hole length (Maximum) | 61.5 mm           |
| Plate hole width (Minimum)  | 46.5 mm           |
| Plate hole width (Maximum)  | 51.5 mm           |
| Plate hole diameter         | 8.5 mm            |



Deutscher Designer Club



Interzum Award



IF Design Award

PRODUCT INFORMATION

# LINEA

5947UAC125P50 RAL9002


EAN 4031582353099



BETTER MOBILITY. BETTER LIFE.

TECHNICAL DRAWINGS

---



Deutscher  
Designer  
Club



Interzum  
Award



IF  
Design  
Award